

Garant**APMT 060208 ER, HB8630, Type: INOX****Order data**

Order number	215670 INOX
GTIN	4045197747563
Item class	21A

Description**Note:**

Standard application values for $a_e = 0.25 \times D$. $a_p = 3$ mm, a_p max = 4 mm.

Technical description

Type	INOX
Feed f_z per tooth	0.08 mm
Corner radius	0.8 mm
Series	Softcut®
ISO code indexable insert	APMT 060208 ER
Grade	HB8630
Tool material	Carbide
Type of product	Indexable insert for milling

User data

	Suitability	V_c	ISO code
INOX < 900 N/mm ²	suitable	170 m/min	M
INOX > 900 N/mm ²	suitable	130 m/min	M
wet maximum	suitable only under restricted conditions		
dry	suitable		