

**Garant**
**Solid carbide copy milling cutter extra long, Plain shank, Ø D: 16mm**

**Order data**

Order number	212592 16
GTIN	4045197761477
Item class	210

**Description**
**Version:**

Exactly accurate insert bedding due to optimised design of insert and insert seat tolerances. Highest interchange accuracy guaranteed:  $\pm 0.015$  mm.

**Application:**

General use for finishing and semi-finishing operations.

**Solid carbide** – for large depths of cut and to minimise vibration.

**Note:**

Calculate the speed based on the effective  $\varnothing D_w$ . Use GARANT torque screwdriver TQ No. **211750 size 3.0** with bit No. **674252 size 15IP**.

**Technical description**

Number of cutting edges Z	2
Shank $\varnothing D_s$ h6	16 mm
Overhang $L_1$	55 mm
$\varnothing d_1$	14 mm
Cutting edge $\varnothing D_c$	16 mm
Overall length $L_{tot}$	175 mm
Insert screw	219873 (15IP; 3.0 Nm)
Through-coolant	yes
Shank type	Plain shank
Milling application	Copy milling

Tool exchange	PowerCard
Type of product	Copy mill

---

## Accessories

Clamping screw	219872
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 15IP	674252 15IP
Torque screwdriver, fixed setting set torque 3,0 N·m	211750 3,0