

Garant
Face mill arbor vibration-damped, cylindrical, HSK-A 100 A = 200, Spigot Ø d1: 22mm

Order data

| | |
|--------------|---------------|
| Order number | 306708 22 |
| GTIN | 4045197761996 |
| Item class | 31A |

Description
Version:

- Taper shank, spigot, and all contact surfaces are ground at the collar.
- With Balluff/RFID chip bore.
- Increased collar contact surface.

Vibration damped version, arbor with vibration-damping core.

Advantage:

Significantly lower tendency to vibrate! Considerable increase in feed rate!

Supplied with:

Cutter lock screw and drive dog.

Optional extras:

Special coolant pipe wrench No. 309840, coolant pipe No. 309880.

Note:

Further sizes on request.

Technical description

| | |
|---------------------------------------|-------------------|
| Ø D ₂ | 48 mm |
| Overhang dimension A | 200 mm |
| Milling mandrel length L ₄ | 19 mm |
| Adapter | HSK-A 100 A = 200 |
| Standard | DIN 6357 |

| | |
|---------------------------------------|--------------------|
| Arbor standard | DIN 69882-3 |
| Arbor standard | DIN 69893 |
| Arbor standard | ISO 12164-1 |
| Shape | A |
| Balance quality G at rotational speed | G 6.3 at 8,000 rpm |
| Concentricity | ≤ 6 μm |
| Machining strategy | HPC |
| Vibration | damped |
| Type of product | Milling head arbor |

Accessories

| | |
|------------------------------------|-----------|
| Toggle spanner for mandrel Ø 22 mm | 309840 22 |
|------------------------------------|-----------|