



Short drill chuck Form A, BT 30, Clamping range: 0,5-13mm



Order data

Order number	303196 0,5-13
GTIN	2050001839022
Item class	33W

Description

Version:

For clockwise and anticlockwise rotation.

Supplied with:

Clamping wrench.

Optional extras:

Pull studs (PS) No. 308760 – 308806. Pull stud wrenches No. 308820; 308835.

Technical description

Overhang dimension A	96 mm
Spare chuck key No. 627425	6 AF
Clamping range	0.5 - 13 mm
External Ø D	50 mm
Adapter	BT 30
Arbor standard	ISO 7388-2
Arbor standard	JIS B6339
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 30 µm
Type of product	Short drill chuck

Accessories

Pull stud 45°sealed suitable for steep tapers 30	308760 30
Pull stud 60°sealed suitable for steep tapers 30	308785 30
Hexagon screwdriver, with T-handle Hexagon 4 mm	627481 4
Pull stud 45°sealed suitable for steep tapers 30	308765 30