

**Garant**

**Shrink-fit chuck 3°, slim, HSK-A 63 A = 120, Clamping range Ø D1: 5mm**


**Order data**

Order number	308318 5
GTIN	4045197762658
Item class	31A

**Description**
**Version:**

- **All shanks hard turned (for smooth running!).**
- **HSK mating faces machined.**
- **Slim design (3° contour).**

**Balancing quality 2.5 / 25,000 rpm.** With RFID/Balluffchip bore.

**Application:**

- **Especially in tool and mould making.**
- **For clamping tools with shank tolerance h6.**

**Optional extras:**

Coolant tube No. 309880. Socket No. 309890. Shrink-fit chuck extensions No. 302410 sizes 12/3 and 12/4. Shrink-fitting units No. 354210 – 354450.

**Technical description**

Clamping Ø D <sub>1</sub>	5 mm
Overhang dimension A	120 mm
External Ø D	21 mm
Ø D <sub>2</sub>	11 mm
Adapter	HSK-A 63 A = 120
Arbor standard	DIN 69893
Arbor standard	ISO 12164-1

Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HSC
Type of product	Shrink-fit chuck

## Accessories

Subframe cupboard	354290
Shrink-fit unit Type SU1	354210 SU1
Cooling adapter long $4.5^\circ$ for clamping $\varnothing$ 3-5,9 mm	354236 3-5,9
Cooling unit Type CU1	354215 CU1
Screening plate for coilSU1 for clamping $\varnothing$ 3-5 mm	354240 3-5
Cooling adapter short $4.5^\circ$ for clamping $\varnothing$ 3-5,9 mm	354235 3-5,9