

PRYOR

Numeral punch set, 10 pieces Normal script 0 – 9, Character height: 8mm



Order data

Order number	085405 8
GTIN	5022044004283
Item class	08W

Description

Version:

Made of hard and tough steel with particularly precise machine engraving and depth tolerance; accurately centred. Calibrated shank, through hardened. Striking head enhancement for safe working. Supplied in a plastic case.

High performance precision punches, chemically nickel-plated, very long service life.

Normal script; i. e. the punched character can be read directly on the component.

Application:

For punching into materials with a **strength up to 1200 N/mm²**.

Spare part:

Individual number punches under No. 085411 size font height/number, e. g. No. 085411 size 3/1.

Individual letter punches under No. 085431 size font height/character, e.g. No. 085431 size 3/A.

Note:

Other hand and machine punches of all types, such as punches with a company's logo etc., are available on request.

Technical description

Shank thickness	12.7
-----------------	------

Depth limitation	yes
overall length	89 mm
Character height	8 mm
Type of product	Hand punch

Accessories

Number punch – individual Normal script 0 – 9 Font height (mm) / characters 8/2	085411 8/2
Number punch – individual Normal script 0 – 9 Font height (mm) / characters 8/6	085411 8/6
Number punch – individual Normal script 0 – 9 Font height (mm) / characters 8/4	085411 8/4
Number punch – individual Normal script 0 – 9 Font height (mm) / characters 8/3	085411 8/3
Number punch – individual Normal script 0 – 9 Font height (mm) / characters 8/7	085411 8/7
Number punch – individual Normal script 0 – 9 Font height (mm) / characters 8/8	085411 8/8
Punch holder Type GRIP	085475 GRIP
Number punch – individual Normal script 0 – 9 Font height (mm) / characters 8/5	085411 8/5
Number punch – individual Normal script 0 – 9 Font height (mm) / characters 8/1	085411 8/1
Number punch – individual Normal script 0 – 9 Font height (mm) / characters 8/0	085411 8/0
Number punch – individual Normal script 0 – 9 Font height (mm) / characters 8/9	085411 8/9