

**Garant**
**Side lock arbor, HSK-A 100 short, Clamping range Ø D1: 40mm**

**Order data**

Order number	304390 40
GTIN	4045197762740
Item class	31A

**Description**
**Version:**

- With RFID/Balluffchip bore.
- HSK mating faces machined.

**GARANT:** All shanks hard turned (for smooth cutting action!).

**Application:**

For clamping tools with Weldon shank to DIN 1835 Form B and DIN 6535 Form HB.

**Optional extras:**

Coolant pipe No. 309880, coolant pipe wrench No. 309890

**Note:**

HSK 40 and 50, Form A and E available ex works by the manufacturer.

**Technical description**

Spare clamping screw No. 30 9900	32
External Ø D	80 mm
Overhang dimension A	120 mm
Clamping Ø D <sub>1</sub>	40 mm
Adapter	HSK-A 100 short
Arbor standard	DIN 69893
Arbor standard	DIN 69882-4

Arbor standard	ISO 12164-1
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HPC
Machining strategy	HSC
Type of product	Side lock arbor

---

## Accessories

HSK coolant tube for HSK 40	309880 40
Spare clamping screw for chucks with clamping $\varnothing$ D1 32 mm	309900 32
Socket wrench for coolant tubes for HSK 40	309890 40