

**Garant****Grooving toolholder, left-hand, Shank size: 25mm****Order data**

Order number	273911 25
GTIN	4045197763129
Item class	21W

**Description****Note:**

For **right-hand toolholders** use **right-hand inserts**, for **left-hand toolholders** use **left-hand inserts**.

**Technical description**

Head length L <sub>1</sub>	21.4 mm
Shank size	25 mm
Insert screw	279815 13
Overall length L	150 mm
Free length	1.2 mm
Functional width L <sub>4</sub>	30.2 mm
Application type	left-hand
Through-coolant	no
axial grooving possible	no
Type of product	Boring bar

**Accessories**

Clamping screw Type 13	279815 13
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500