

**Garant****Boring bar, right-hand, Shank Ø DS: 25mm****Order data**

Order number	273914 25
GTIN	4045197763136
Item class	21W

**Description****Note:**

For **right-hand toolholders** use **left-hand inserts**, for **left-hand toolholders** use **right-hand inserts**.

**Technical description**

Overall length L	250 mm
Minimum pre-drill Ø D <sub>min</sub>	30.5 mm
Insert height L <sub>2</sub>	11.5 mm
Insert screw	279815 13
Centre offset L <sub>3</sub>	17.5 mm
Shank Ø D <sub>s</sub>	25 mm
Application type	right-hand
Type of product	Boring bar

**Accessories**

Clamping screw Type 13	279815 13
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15

Torque screwdriver with scale, to take interchangeable  
blades maximum torque 500 cNm

---

659957 500