

**Garant****Boring bar, left-hand, Shank Ø DS: 25mm****Order data**

Order number	273915 25
GTIN	4045197763167
Item class	21W

**Description****Note:**

For **right-hand toolholders** use **left-hand inserts**, for **left-hand toolholders** use **right-hand inserts**.

**Technical description**

Minimum pre-drill $\varnothing D_{\min}$	30.5 mm
Insert screw	279815 13
Insert height $L_2$	11.5 mm
Overall length $L$	250 mm
Centre offset $L_3$	17.5 mm
Shank $\varnothing D_s$	25 mm
Application type	left-hand
Type of product	Boring bar

**Accessories**

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Clamping screw Type 13	279815 13

## Data sheet

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

---

659957 500