



Knurl forming tool right-hand, Shank size: 16mm



Order data

Order number	290000 16
GTIN	4030741659652
Item class	29H

Description

Version:

Top face of the shank = tip height

Grub screw in the shank for clearance angle correction.

Carbide roller pin for increased wear resistance.

Click-Pin: For quick and easy changing of the knurl.

Technical description

Shank width	16 mm
Working range	3 - 50 mm
for knurl bore $\varnothing d_2$	4 mm
Shank height	16 mm
Roller pin	299910 2
for knurl $\varnothing d_1$	15 mm
for knurl $\varnothing d_1$	10 mm
for knurl width w	4 mm
for knurl profile	RGV30° 1×GE30°
for knurl profile	RGE30° 1×GV30°
for knurl profile	RAA 1×AA
for knurl profile	RBR 1×BL

for knurl profile	RBL 1×BR
Type of product	Self-centering knurling tool

Accessories

Carbide roller pin Carbide Type 1	299910 1
-----------------------------------	----------