



## Knurl forming tool universal, Shank size: 12mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 290010 12     |
| GTIN         | 4030741657849 |
| Item class   | 29H           |

### Description

#### Version:

Grub screw in the shank for clearance angle correction.

Carbide roller pin for increased wear resistance.

**Modular design: Can be used as a right-hand or left-hand version.**

### Technical description

|                                  |                          |
|----------------------------------|--------------------------|
| Shank height                     | 12 mm                    |
| for knurl width w                | 4 mm                     |
| for knurl bore $\varnothing d_2$ | 4 mm                     |
| Working range                    | 3 - 25 mm                |
| Roller pin                       | 299910 5                 |
| for knurl $\varnothing d_1$      | 10 mm                    |
| Shank width                      | 12 mm                    |
| Cutting direction                | left-hand and right-hand |
| for knurl profile                | RBR 2×BL                 |
| for knurl profile                | RAA 2×AA                 |
| for knurl profile                | RBL 2×BR                 |
| for knurl profile                | RGE30° BL/BR30°          |

|                   |                              |
|-------------------|------------------------------|
| for knurl profile | RGE45° BL/BR45°              |
| Type of product   | Self-centering knurling tool |

---

## Accessories

|                                   |          |
|-----------------------------------|----------|
| Carbide roller pin Carbide Type 5 | 299910 5 |
|-----------------------------------|----------|