



Knurl forming tool universal, Shank size: 16mm



Order data

Order number	290010 16
GTIN	4030741324437
Item class	29H

Description

Version:

Grub screw in the shank for clearance angle correction.

Carbide roller pin for increased wear resistance.

Modular design: Can be used as a right-hand or left-hand version.

Technical description

Working range	6 - 60 mm
Roller pin	299910 6
Shank width	16 mm
Shank height	16 mm
for knurl bore $\varnothing d_2$	4 mm
for knurl width w	6 mm
for knurl $\varnothing d_1$	15 mm
Cutting direction	left-hand and right-hand
for knurl profile	RBR 2×BL
for knurl profile	RAA 2×AA
for knurl profile	RBL 2×BR
for knurl profile	RGE30° BL/BR30°

for knurl profile	RGE45° BL/BR45°
Type of product	Self-centering knurling tool

Accessories

Carbide roller pin Carbide Type 6	299910 6
-----------------------------------	----------