



ECO knurl forming tool universal, Shank size: 16 mm



Order data

Order number	290035 16
GTIN	4030741007880
Item class	29I

Description

Version:

Used conventionally.

Note:

Tip height must be adjusted.

for knurl profile: RGV30° 1×GE30°

for knurl $\varnothing d_1$: 20 mm

for knurl width w: 8 mm

for knurl bore $\varnothing d_2$: 6 mm

Working range: 15 - 200 mm

Roller pin: 299911 1

Technical description

Roller pin	299911 1
for knurl bore $\varnothing d_2$	6 mm
for knurl width w	8 mm
Working range	15 - 200 mm
for knurl $\varnothing d_1$	20 mm
Shank height	16 mm
Shank width	16 mm
Cutting direction	left-hand and right-hand
for knurl profile	RGE30° 1×GV30°

for knurl profile	RBR 1×BL
for knurl profile	RAA 1×AA
for knurl profile	RBL 1×BR
for knurl profile	RGV30° 1×GE30°
Type of product	Self-centering knurling tool

Accessories

HSS roller pin	290300
HSS roller pin HSS Type 1	299911 1
ECO knurl forming tool set Type SET	290050 SET