



Knurl forming tool set, Shank / insert size: 12mm



Order data

Order number	290025 12
GTIN	4030741656767
Item class	29H

Description

Content:

- 1 pc. each knurl forming tool No. 290000 and No. 290010: Size 12
- 2 pcs. each knurl No. 290161: Size 10×4/0.5; 10×4/0.6; 10×4/0.8
- 1 pc. each knurl No. 290176 and No. 290181: Size 10×4/0.5; 10×4/0.6; 10×4/0.8
- 1 pc. each knurl No. 290161: Size 15×4/0.5; 15×4/0.6; 15×4/0.8

Technical description

Cutting direction	left-hand and right-hand
for knurl profile	RBL 2×BR
for knurl profile	RBR 2×BL
for knurl profile	RBL 1×BR
for knurl profile	RAA 2×AA
for knurl profile	RBR 1×BL
for knurl profile	RGV30° 1×GE30°
for knurl profile	RGE30° 1×GV30°

for knurl profile	RBL 1×BR
for knurl profile	RGE30° BL/BR30°
for knurl profile	RGE45° BL/BR45°
Type of product	Self-centering knurling tool

Accessories

Knurl forming toolright-hand Shank size 10 mm	290000 10
Knurl PM Knurl Ø d1 × knurl width b / pitch 10X4/0,8 mm	290176 10X4/0,8
Knurl PM Knurl Ø d1 × knurl width b / pitch 10X4/0,8 mm	290181 10X4/0,8
Knurl PM Knurl Ø d1 × knurl width b / pitch 10X4/0,5 mm	290176 10X4/0,5
Knurl PM Knurl Ø d1 × knurl width b / pitch 10X4/0,6 mm	290176 10X4/0,6
Knurl forming toolright-hand Shank size 12 mm	290000 12
Knurl PM Knurl Ø d1 × knurl width b / pitch 10X4/0,5 mm	290181 10X4/0,5
Knurl PM Knurl Ø d1 × knurl width b / pitch 10X4/0,8 mm	290161 10X4/0,8
Knurl forming tooluniversal Shank size 10 mm	290010 10
Knurl PM Knurl Ø d1 × knurl width b / pitch 10X4/0,6 mm	290161 10X4/0,6
Knurl PM Knurl Ø d1 × knurl width b / pitch 10X4/0,5 mm	290161 10X4/0,5
Knurl forming tooluniversal Shank size 12 mm	290010 12
Knurl forming toolleft-hand Shank size 10 mm	290001 10
Knurl PM Knurl Ø d1 × knurl width b / pitch 10X4/0,6 mm	290181 10X4/0,6