



## Knurl forming tool set, Shank / insert size: 16mm



### Order data

Order number	290025 16
GTIN	4030741656842
Item class	29H

### Description

#### Content:

1 pc. each knurl forming tool No. 290000 and No. 290010: Size 16

3 pc. each knurl No. 290161: Size 15×4/0.6; 15×4/0.8; 15×4/1.0

1 pc. each knurl No. 290176 and No. 290181: Size 15×4/0.6; 15×4/0.8; 15×4/1.0

### Technical description

Cutting direction	left-hand and right-hand
for knurl profile	RBL 2×BR
for knurl profile	RBR 2×BL
for knurl profile	RBL 1×BR
for knurl profile	RAA 2×AA
for knurl profile	RBR 1×BL
for knurl profile	RGV30° 1×GE30°
for knurl profile	RGE30° 1×GV30°
for knurl profile	RBL 1×BR

for knurl profile	RGE30° BL/BR30°
for knurl profile	RGE45° BL/BR45°
Type of product	Self-centering knurling tool

## Accessories

Knurl PM Knurl Ø d1 × knurl width b / pitch 15X4/0,8 mm	290161 15X4/0,8
Knurl PM Knurl Ø d1 × knurl width b / pitch 15X4/0,8 mm	290181 15X4/0,8
Knurl PM Knurl Ø d1 × knurl width b / pitch 15X4/0,6 mm	290161 15X4/0,6
Knurl forming tooluniversal Shank size 16 mm	290010 16
Knurl PM Knurl Ø d1 × knurl width b / pitch 15X4/0,5 mm	290161 15X4/0,5
Knurl PM Knurl Ø d1 × knurl width b / pitch 15X4/0,8 mm	290176 15X4/0,8
Knurl PM Knurl Ø d1 × knurl width b / pitch 15X4/0,6 mm	290176 15X4/0,6
Knurl PM Knurl Ø d1 × knurl width b / pitch 15X4/0,6 mm	290181 15X4/0,6
Knurl PM Knurl Ø d1 × knurl width b / pitch 15X4/0,5 mm	290181 15X4/0,5
Knurl PM Knurl Ø d1 × knurl width b / pitch 15X4/0,5 mm	290176 15X4/0,5
Knurl forming toolright-hand Shank size 16 mm	290000 16