



Cut knurling tool set, Shank size: 20mm



Order data

Order number	290219 20
GTIN	4030741656903
Item class	29H

Description

Version:

Modular design: Can be used universally as right-hand or left-hand version.

Carbide running sleeve for increased wear resistance.

Quick tool adjustment by using the adjustment spindle.

Content:

1 pc. each knurling tool No. 290200 and No. 290210: Size 20

1 pc. each knurl No. 290276 and No. 290281: Size 25×6/0.8; 25×6/1.0; 25×6/1.5

2 pc. each knurl No. 290261: Size 25×6/0.8; 25×6/1.0; 25×6/1.5

Technical description

Cutting direction	left-hand and right-hand
for knurl profile	RBL45° 1×BR15°
for knurl profile	RBL30° 1×AA
for knurl profile	RBR45° 1×BL15°
for knurl profile	RAA 1×BL30°
for knurl profile	RBR30° 1×AA

for knurl profile	RBL30° 1×AA
for knurl profile	RGE30° 2×AA
for knurl profile	RGE45° BL/BR45°
Type of product	Self-centering knurling tool

Accessories

Cut knurling tooluniversal Shank size 16X mm	290210 16X
Knurl PM Knurl Ø d1 × knurl width w / pitch 25X6/1,0 mm	290261 25X6/1,0
Knurl PM Knurl Ø d1 × knurl width w / pitch 25X6/0,8 mm	290261 25X6/0,8
Cut knurling tooluniversal Shank size 20 mm	290200 20
Knurl PM Knurl Ø d1 × knurl width w / pitch 25X6/1,0 mm	290276 25X6/1,0
Knurl PM Knurl Ø d1 × knurl width w / pitch 25X6/1,5 mm	290261 25X6/1,5
Knurl PM Knurl Ø d1 × knurl width w / pitch 25X6/1,5 mm	290276 25X6/1,5
Cut knurling tooluniversal Shank size 20 mm	290210 20
Knurl PM Knurl Ø d1 × knurl width w / pitch 25X6/0,8 mm	290276 25X6/0,8