



ECO knurling tool right-hand, Shank size: 12mm



Order data

Order number	290230 12
GTIN	4030741341786
Item class	29H

Description

Version:

Grub screws in the shank for clearance angle correction.

for knurl profile: RAA 1×BR30°

for knurl $\varnothing d_1$: 15 mm

for knurl width w: 4 mm

for knurl bore $\varnothing d_2$: 8 mm

Working range: 3 - 50 mm

Carbide sleeve, cover disc, screw: 299920 3

Technical description

Shank height	12 mm
Working range	3 - 50 mm
Shank width	12 mm
Carbide sleeve, cover disc, screw	299920 3
for knurl bore $\varnothing d_2$	8 mm
for knurl $\varnothing d_1$	15 mm
for knurl width w	4 mm
for knurl profile	RAA 1×BR30°
Type of product	Self-centering knurling tool

Accessories

Spare parts kit (3 pieces), carbide bush, cover washer,
screw Type 3

299920 3