

Yale

Electric chain hoist CPVF VEGO, Type: 0,25-8



Order data

Order number	086036 0,25-8
GTIN	2050001940469
Item class	08Y

Description

Version:

Electric chain hoist with **lifting hook** in robust and reliable design. The integral **end-of-travel switch** for the highest and lowest hook positions protects the clutch, motor, and housing and extends their working life. Drive group 1 Am, 50 % duty cycle at one speed, standard operating voltage (400 V / 50 Hz). Enhanced operating safety due to 42 V contactor controls, encapsulated control switches to Index of Protection IP65, motors to IP55.

With two speeds (precision lifting).

Function:

IP55: Protected against jets of water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching. (Applies to the motor).

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching. (Applies to the control switch).

Note:

Versions with 2 speeds (precision lifting) and other lifting heights, power traverse, chain box and radio and 230 V power supply available on request.

Technical description

Standard lifting height	3 m
Safe working load	250 kg
Number of chains	1
Lifting speed	8 m/min
Lifting speed	2 m/min
Weight	18 kg
IP Index of Protection	IP 55
IP Index of Protection	IP 65
Type of product	Lever hoist