

uvex

Shoe, black/orange uvex 2, S3, EU shoe size: 39



Order data

| | |
|--------------|---------------|
| Order number | 092135 39 |
| GTIN | 4031101609515 |
| Item class | 04V |

Description

Version:

Lightweight and flexible safety shoe. Suitable for wearers allergic to chromium. Width 11.

- **Distance Mesh lining material.**
- **100 % metal-free uvex xenova® toecap.**
- **Two-layer PU sole with TPU inserts with the best damping characteristics.**
- **PU overcap to protect the upper material, for significantly longer working life.**
- **Virtually seamless design to avoid pressure points.**
- **ESD security.**

Safety shoes of hydrophobic, fully grained smooth leather and elastic laces with quick fastening. With non-metallic penetration-resistant insert.

Standard:

EN ISO 20345:2011 S3 SRC

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

electrostatic characteristic: EGB/ESD

Protection class: S3

Material of protective toe-cap: Composite

Puncture resistance: Textile

Standard: Inlay type-tested according to DGUV regulation 191

Technical description

| | |
|---------------------|---------|
| Puncture resistance | Textile |
|---------------------|---------|

| | |
|--|--|
| Material inner lining | Distance Mesh |
| Material of protective toe-cap | Composite |
| EU shoe size | 39 |
| Uppers material | Genuine leather |
| Standard | Inlay type-tested according to DGUV regulation 191 |
| Colour | black/orange |
| against water penetration and water absorption | yes |
| Protection class | S3 |
| Series | uvex 2 |
| Gender | Gentlemen's |
| electrostatic characteristic | EGB/ESD |
| Type of product | Safety shoes |