

**Garant**
**Grooving toolholder, right-hand, Shank width / groove width w: 10/1,5mm**

**Order data**

Order number	273755 10/1,5
GTIN	4045197766076
Item class	21W

**Description**
**Version:**

Made of high-tensile tool steel ( $> 1300 \text{ N/mm}^2$ ). In conjunction with the convex insert clamping, the system achieves very high resistance to axial and radial cutting forces and thereby significantly increases the surface quality and productivity.

**Note:**

From groove width 6 mm at  $t_{\max}$  ( $5 \times$  groove width), the second cutter comes into contact with the workpiece. This can lead to scoring. Reliably free of scoring up to  $t = 24.5 \text{ mm}$ .

**Technical description**

Groove width w	1.5 mm
Screw	279815 4 (TX15; 3.5 Nm)
Grooving depth $t_{\max}$	7.5 mm
Head length $L_1$	20.5 mm
Functional width $L_4$	10 mm
Overall length L	120 mm
Shank width b	10 mm
Application type	right-hand
Through-coolant	no
axial grooving possible	yes

Type of product

Boring bar

---

**Accessories**

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15

674248 TX15

Clamping screw Type 4

279815 4

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500