

Garant
Screw-in shrink adapter slim, Thread M × clamping Ø D1: M12X10

Order data

Order number	301397 M12X10
GTIN	4045197767363
Item class	31Z

Description
Version:

High-temperature steel, integral length adjustment of the tools, extra slim design, for HSS and carbide.

Application:

Flexible use on the most demanding applications for accuracy and balancing speed, e.g. in combination with extensions.

Technical description

Overhang dimension A	60 mm
Length L	38 mm
External Ø D	24 mm
Extension Ø D ₃	23 mm
Clamping Ø D ₁	10 mm
Ø D ₂	18 mm
Thread M	M12
maximum tightening torque	60 Nm
Through-coolant	yes
Concentricity	≤ 3 µm
Type of product	Reducer

