

Garant
Reducing adapter for PSC shank, HSK-A 63, PSC inner: 4

Order data

Order number	306975 4
GTIN	4045197768933
Item class	31Z

Description
Version:

Ground internally and externally. The internal thread provided for the coolant tube in the PSC toolholder is plugged with the socket-head screw incorporated in the adapter. The clamping screw incorporates a through hole, so the system is suitable for through-coolant feed. With Balluffchip bore.

Application:

For adaption from HSK-A to PSC.

Suitable for :

Tool arbor with **polygonal shank (PSC) – ISO 26623-1**.

Optional extras:

Coolant pipe No. 309880, plug-in socket No. 309890

Overhang dimension A: 80 mm

External Ø D: 40 mm

L₁: 54 mm

Technical description

External Ø D	40 mm
Overhang dimension A	80 mm
L ₁	54 mm
Adapter	HSK-A 63

Arbor standard	DIN 69893
Arbor standard	ISO 12164-1
Arbor standard	ISO 26623-2
Shape	A
Through-coolant	yes
Balance quality G at rotational speed	G 6.3 at 8,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Type of product	Arbor adapter