

**Garant**
**Reducing adapter for PSC shank, HSK-A 63, PSC inner: 5**

**Order data**

Order number	306975 5
GTIN	4045197768940
Item class	31Z

**Description**
**Version:**

Ground internally and externally. The internal thread provided for the coolant tube in the PSC toolholder is plugged with the socket-head screw incorporated in the adapter. The clamping screw incorporates a through hole, so the system is suitable for through-coolant feed. With Balluffchip bore.

**Application:**

For adaption from HSK-A to PSC.

**Suitable for :**

Tool arbor with **polygonal shank (PSC) – ISO 26623-1**.

**Optional extras:**

Coolant pipe No. 309880, plug-in socket No. 309890

Overhang dimension A: 90 mm

External Ø D: 50 mm

L<sub>1</sub>: 64 mm

**Technical description**

External Ø D	50 mm
L <sub>1</sub>	64 mm
Overhang dimension A	90 mm
Adapter	HSK-A 63

Arbor standard	DIN 69893
Arbor standard	ISO 12164-1
Arbor standard	ISO 26623-2
Shape	A
Through-coolant	yes
Balance quality G at rotational speed	G 6.3 at 8,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Type of product	Arbor adapter