

## PRYOR

**Numeral punch set, 10 pieces Normal script 0 – 9, Character height: 10mm**



### Order data

Order number	085405 10
GTIN	5022044004726
Item class	08W

### Description

#### Version:

Made of hard and tough steel with particularly precise machine engraving and depth tolerance; accurately centred. Calibrated shank, through hardened. Striking head enhancement for safe working. Supplied in a plastic case.

**High performance precision punches**, chemically nickel-plated, very long service life.

**Normal script**; i. e. the punched character can be read directly on the component.

#### Application:

For punching into materials with a **strength up to 1200 N/mm<sup>2</sup>**.

#### Spare part:

Individual number punches under No. 085411 size font height/number, e. g. No. 085411 size 3/1.

Individual letter punches under No. 085431 size font height/character, e.g. No. 085431 size 3/A.

#### Note:

Other hand and machine punches of all types, such as punches with a company's logo etc., are available on request.

### Technical description

Depth limitation	yes
------------------	-----

Shank thickness	14.3
Character height	10 mm
overall length	89 mm
Type of product	Hand punch

## Accessories

Punch holder Type GRIP	085475 GRIP
Number punch – individual Normal script 0 – 9 Font height (mm) / characters 10/0	085411 10/0
Number punch – individual Normal script 0 – 9 Font height (mm) / characters 10/1	085411 10/1
Number punch – individual Normal script 0 – 9 Font height (mm) / characters 10/2	085411 10/2
Number punch – individual Normal script 0 – 9 Font height (mm) / characters 10/3	085411 10/3
Number punch – individual Normal script 0 – 9 Font height (mm) / characters 10/4	085411 10/4
Number punch – individual Normal script 0 – 9 Font height (mm) / characters 10/5	085411 10/5
Number punch – individual Normal script 0 – 9 Font height (mm) / characters 10/6	085411 10/6
Number punch – individual Normal script 0 – 9 Font height (mm) / characters 10/7	085411 10/7
Number punch – individual Normal script 0 – 9 Font height (mm) / characters 10/8	085411 10/8
Number punch – individual Normal script 0 – 9 Font height (mm) / characters 10/9	085411 10/9