


Knurl PM, AA, Knurl \varnothing d1 \times knurl width w / pitch: 21,5X5/0,5mm

Order data

Order number	290261 21,5X5/0,5
GTIN	4030741319785
Item class	29I

Description
Version:

Wear-resistant, of sintered metal.

Note:

- **Size 21.5 \times 5 \times 8 suitable for Quick tools.**
- **Further sizes available on request.**

Knurl bore \varnothing d₂: 8 mm

Technical description

Knurl bore \varnothing d ₂	8 mm
Knurl type	AA
For standard	DIN 82
Tool material	PM
Type of product	Knurling wheel

User data

	Suitability	V_c	ISO code
Alu plastics	suitable	160 m/min	N
Aluminium (short chipping)	suitable	110 m/min	N
Steel < 500 N/mm ²	suitable	110 m/min	P
Steel < 750 N/mm ²	suitable	85 m/min	P
Steel < 900 N/mm ²	suitable	65 m/min	P
INOX < 900 N/mm ²	suitable	60 m/min	M
INOX > 900 N/mm ²	suitable	35 m/min	M
CuZn	suitable	120 m/min	N
Oil	suitable		
wet maximum	suitable only under restricted conditions		
wet minimum	suitable only under restricted conditions		