

**Garant**
**Eccentric clamping sleeve,  $\varnothing d$  H5: 10mm**

**Order data**

Order number	236679 10
GTIN	4045197768964
Item class	21P

**Description**
**Version:**

Adjustment range in the  $\varnothing \pm 0.5$  mm.

For use in conjunction with boring bars (No. 236677) -0.3 / +0.5 mm adjustment range to the nominal  $\varnothing$ .

**Application:**

Tool for boring to "fixed size" in conjunction with precision boring bar. Fitted in side lock arbors with Weldon shank  $\varnothing$  25; 32 and 40 mm to DIN 1835 B.

**Note:**

The exact adjustment of the diameter is performed on the pre-setter by rotating the boring bar.

**Technical description**

Overall length $L_{tot}$	62 mm
$\varnothing D_1$	29 mm
$L_1$	57 mm
Tolerance external $\varnothing$	H5
$\varnothing d$	10 mm
$\varnothing D$	25 mm
Type of product	Clamping sleeve

