

Garant
Eccentric clamping sleeve, \varnothing d H5: 16mm

Order data

Order number	236679 16
GTIN	4045197768988
Item class	21P

Description
Version:

Adjustment range in the $\varnothing \pm 0.5$ mm.

For use in conjunction with boring bars (No. 236677) -0.3 / +0.5 mm adjustment range to the nominal \varnothing .

Application:

Tool for boring to "fixed size" in conjunction with precision boring bar. Fitted in side lock arbors with Weldon shank \varnothing 25; 32 and 40 mm to DIN 1835 B.

Note:

The exact adjustment of the diameter is performed on the pre-setter by rotating the boring bar.

Technical description

Tolerance external \varnothing	H5
Overall length L_{tot}	62 mm
$\varnothing D_1$	29 mm
$\varnothing d$	16 mm
$\varnothing D$	25 mm
L_1	57 mm
Type of product	Clamping sleeve

