

Garant**Eccentric clamping sleeve, \varnothing d H5: 20mm****Order data**

Order number	236679 20
GTIN	4045197768995
Item class	21P

Description**Version:**

Adjustment range in the $\varnothing \pm 0.5$ mm.

For use in conjunction with boring bars (No. 236677) -0.3 / +0.5 mm adjustment range to the nominal \varnothing .

Application:

Tool for boring to "fixed size" in conjunction with precision boring bar. Fitted in side lock arbors with Weldon shank \varnothing 25; 32 and 40 mm to DIN 1835 B.

Note:

The exact adjustment of the diameter is performed on the pre-setter by rotating the boring bar.

Technical description

\varnothing d	20 mm
Tolerance external \varnothing	H5
L_1	61 mm
$\varnothing D_1$	36 mm
$\varnothing D$	32 mm
Overall length L_{tot}	66 mm
Type of product	Clamping sleeve

