

Garant
Eccentric clamping sleeve, $\varnothing d$ H5: 32mm

Order data

Order number	236679 32
GTIN	4045197769114
Item class	21P

Description
Version:

Adjustment range in the $\varnothing \pm 0.5$ mm.

For use in conjunction with boring bars (No. 236677) -0.3 / +0.5 mm adjustment range to the nominal \varnothing .

Application:

Tool for boring to "fixed size" in conjunction with precision boring bar. Fitted in side lock arbors with Weldon shank $\varnothing 25$; 32 and 40 mm to DIN 1835 B.

Note:

The exact adjustment of the diameter is performed on the pre-setter by rotating the boring bar.

Technical description

$\varnothing D$	40 mm
Overall length L_{tot}	76 mm
$\varnothing d$	32 mm
L_1	71 mm
$\varnothing D_1$	44 mm
Tolerance external \varnothing	H5
Type of product	Clamping sleeve

