

Garant
Precision boring bar, DIN 1835 A, Nominal \varnothing D: 14,8mm

Order data

Order number	236677 14,8
GTIN	4045197769176
Item class	21S

Description
Application:

For boring our pre-drilled or cast holes to the nominal \varnothing in combination with eccentric sleeve No. 236679.

For standard ISO indexable inserts CC..0602.

Note:

The \varnothing to be bored out must not be less than D_{\min} .

Technical description

Shank $\varnothing D_s$ h6	12 mm
Pack of insert screws	269410 (7IP; 1.0 Nm)
Minimum $\varnothing d_{\min}$	13.8 mm
Overall length L_{tot}	120 mm
suitable indexable insert	260142 HB725
Overhang L_1	28 mm
Adjustment range with eccentric clamping sleeve	14.5 - 15.3 mm
suitable eccentric clamping sleeve size No. 236679	12
Number of cutting edges Z	1
Nominal $\varnothing D$	14.8
Point angle	180 degrees
Shank type	DIN 1835 A

Through-coolant	yes
Type of product	Indexable drill

Accessories

Torque screwdriver, fixed setting set torque 1,0 N·m	211750 1,0
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 7IP	674252 7IP