

## Boring bar base body vibration damped, 10×D, System / shank Ø: QC/20



### Order data

Order number	264904 QC/20
GTIN	4251414902275
Item class	29E

### Description

**Version:**

With cooling water connection 1/8-27 NPT.

**Supplied with:**

Reducing adaptor from G1/4 inch to G1/8 inch.

**Note:**

Do not clamp on the area marked "S"!

$D_{min} = 1/2 \text{ shank } \varnothing + H + \text{cutting head centre-line offset}$

Through-coolant: yes

System: QC

Overall length  $L_{tot}$ : 260 mm

non-clamping range S: 136.5 mm

recommended clamping length: 80 mm

Assembly bolt: 269025 2

### Technical description

recommended clamping length	80 mm
System	QC
non-clamping range S	136.5 mm
Shank Ø	20 mm
Overall length $L_{tot}$	260 mm
Assembly bolt	269025 2
Boring depth up to	10×D
Vibration	damped

Through-coolant	yes
-----------------	-----

---

## Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cN·m	659906 500
Blade for hexagon, shank E 6.3 Hexagon 2 mm	674242 2