

Boring bar base body Steel DM, 5×D, System / shank Ø: DM/50



Order data

Order number	264910 DM/50
GTIN	4251414902152
Item class	29E

Description

Version:

With cooling water connection 1/8-27 NPT.

Note:

$D_{min} = 1/2 \text{ shank } \varnothing + H + \text{cutting head centre-line offset } L_3.$

Through-coolant: yes

System: DM

Overall length L: 418 mm

Centre offset H base body: 5 mm

Assembly bolt: 269025 1

Technical description

Shank Ø	50 mm
Centre offset H base body	5 mm
System	DM
Assembly bolt	269025 1
High-pressure connecting hose	269207
Plug connector for coolant connection	269208
Overall length L	418 mm
suitable indexable insert	264838; 264839
Boring depth up to	5×D
Through-coolant	yes
Type of product	Boring bar shanks

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659906 500

PrecisionBit for hex, shank E 6.3 Hexagon 2 mm

674242 2