

Cutting head, left-hand, System / insert size: DM/16



Order data

Order number	261322 DM/16
GTIN	4251414902961
Item class	29D

Description

Version:

Interchangeable cutting heads for **vibration-damping base bodies**.

Application:

Vibration damping effect up to a maximum overhang of **14×D**.

Through-coolant: yes

System: DM

ISO code indexable cutting head: SVUCR/L 16

suitable indexable insert: VC.. 1604..

suitable base body: 264910 – 264922

Minimum pre-drill $\varnothing D_{\min}$: 49 mm

Centre-line offset: 27 mm

Overall length: 32 mm

Technical description

suitable indexable insert	VC.. 1604..
Centre-line offset	27 mm
Minimum pre-drill $\varnothing D_{\min}$	49 mm

suitable base body	264910 – 264922
ISO code indexable cutting head	SVUCR/L 16
Overall length	32 mm
System	DM
Insert size	16 mm
Insert screw	269023 3
Series	Cutting head
Application type	left-hand
Through-coolant	yes

Accessories

Clamping screw	269433
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cN·m	659906 500
Torx® bit, shank E 6.3 Torx® profile TX15	674248 TX15