

Cutting head, right-hand, System / insert size: QC/07



Order data

Order number	260405 QC/07
GTIN	4251414902503
Item class	29D

Description

Version:

Interchangeable cutting heads for **vibration-damping base bodies**.

Application:

Vibration damping effect up a maximum overhang of **14xD**.

Through-coolant: yes

System: QC

ISO code indexable cutting head: SDQCR/L 0702

suitable indexable insert: DC.. 0702..

suitable base body: 264900 – 264908

Minimum pre-drill $\varnothing D_{\min}$: 24 mm

Centre-line offset: 13 mm

Overall length: 20 mm

Technical description

Insert screw	269023 1
suitable base body	264900 – 264908
suitable indexable insert	DC.. 0702..

Overall length	20 mm
ISO code indexable cutting head	SDQCR/L 0702
Minimum pre-drill $\varnothing D_{\min}$	24 mm
Centre-line offset	13 mm
System	QC
Insert size	7 mm
Series	Cutting head
Application type	right-hand
Through-coolant	yes

Accessories

Clamping screw	269431
Torx® bit, shank E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cN·m	659906 500