

Boring bar base body Steel DM, 5×D, System / shank Ø: DM/60



Order data

| | |
|--------------|---------------|
| Order number | 264910 DM/60 |
| GTIN | 4251414902206 |
| Item class | 29E |

Description

Version:

With cooling water connection 1/8-27 NPT.

Note:

$D_{min} = 1/2 \text{ shank } \varnothing + H + \text{cutting head centre-line offset } L_3.$

Through-coolant: yes

System: DM

Overall length L: 508 mm

Centre offset H base body: 10 mm

Assembly bolt: 269025 1

Technical description

| | |
|---------------------------------------|-------------------|
| Centre offset H base body | 10 mm |
| Shank Ø | 60 mm |
| System | DM |
| Assembly bolt | 269025 1 |
| High-pressure connecting hose | 269207 |
| Plug connector for coolant connection | 269208 |
| Overall length L | 508 mm |
| suitable indexable insert | 264838; 264839 |
| Boring depth up to | 5×D |
| Through-coolant | yes |
| Type of product | Boring bar shanks |

Accessories

PrecisionBit for hex, shank E 6.3 Hexagon 2 mm

674242 2

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659906 500