

## Cutting head, left-hand, System / insert size: QC/11



### Order data

Order number	261322 QC/11
GTIN	4251414902978
Item class	29D

### Description

#### Version:

Interchangeable cutting heads for **vibration-damping base bodies**.

#### Application:

Vibration damping effect up to a maximum overhang of **14×D**.

Through-coolant: yes

System: QC

ISO code indexable cutting head: SVUCR/L 11

suitable indexable insert: VC.. 1103..

suitable base body: 264900 – 264908

Minimum pre-drill  $\varnothing D_{\min}$ : 26 mm

Centre-line offset: 16 mm

Overall length: 20 mm

### Technical description

Insert size	11 mm
Overall length	20 mm
ISO code indexable cutting head	SVUCR/L 11

Centre-line offset	16 mm
suitable base body	264900 – 264908
suitable indexable insert	VC.. 1103..
System	QC
Minimum pre-drill $\varnothing D_{\min}$	26 mm
Pack of insert screws	269028 7
Series	Cutting head
Application type	left-hand
Through-coolant	yes

## Accessories

Torx® bit, shank E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cN·m	659906 500