

Boring bar base body vibration damped, 12×D, System / shank Ø: QC/20



Order data

Order number	264906 QC/20
GTIN	4251414902282
Item class	29E

Description

Version:

With cooling water connection 1/8-27 NPT.

Shank carbide reinforced.

Supplied with:

Reducing adaptor from G1/4 inch to G1/8 inch.

Note:

Do not clamp on the area marked **S**!

$D_{min} = 1/2 \text{ shank } \varnothing + H + \text{cutting head centre-line offset}$

Through-coolant: yes

System: QC

Overall length L_{tot} : 300 mm

non-clamping range S: 136.5 mm

recommended clamping length: 80 mm

Assembly bolt: 269025 2

Technical description

System	QC
Shank Ø	20 mm
non-clamping range S	136.5 mm
Overall length L_{tot}	300 mm
recommended clamping length	80 mm
Assembly bolt	269025 2
Boring depth up to	12×D
Vibration	damped

Through-coolant	yes
-----------------	-----

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cN·m	659906 500
Blade for hexagon, shank E 6.3 Hexagon 2 mm	674242 2