

Cutting head, right-hand, System / insert size: QC/16



Order data

Order number	260916 QC/16
GTIN	4251414902749
Item class	29D

Description

Version:

Interchangeable cutting heads for **vibration-damping base bodies**.

Application:

Vibration damping effect up a maximum overhang of **14xD**.

Through-coolant: yes

System: QC

ISO code indexable cutting head: STUCR/L 16

suitable indexable insert: TC.. 16T3..

suitable base body: 264900 – 264908

Minimum pre-drill $\varnothing D_{\min}$: 26 mm

Centre-line offset: 15 mm

Overall length: 21 mm

Technical description

Centre-line offset	15 mm
suitable base body	264900 – 264908
ISO code indexable cutting head	STUCR/L 16

Insert size	16 mm
Overall length	21 mm
Insert screw	269023 2
suitable indexable insert	TC.. 16T3..
Minimum pre-drill $\varnothing D_{\min}$	26 mm
System	QC
Series	Cutting head
Application type	right-hand
Through-coolant	yes
Setting angle κ	93 degrees
Application	Internal longitudinal turning

Accessories

Clamping screw	269432
Torx® bit, shank E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cN·m	659906 500