

## Boring bar base body Steel QC, 5×D, System / shank Ø: QC/25



### Order data

Order number	264900 QC/25
GTIN	4251414902305
Item class	29E

### Description

#### Version:

With cooling water connection 1/8-27 NPT.

#### Note:

$D_{min} = 1/2 \text{ shank } \varnothing + H + \text{cutting head centre-line offset } L_3.$

Through-coolant: yes

System: QC

Overall length L: 205 mm

Centre offset H base body: 2.5 mm

Assembly bolt: 269025 2

### Technical description

Shank Ø	25 mm
System	QC
Centre offset H base body	2.5 mm
Assembly bolt	269025 2
Plug connector for coolant connection	269208
High-pressure connecting hose	269207
Overall length L	205 mm
suitable indexable insert	264834; 264835
Boring depth up to	5×D
Through-coolant	yes
Type of product	Boring bar shanks

---

## Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659906 500

PrecisionBit for hex, shank E 6.3 Hexagon 2 mm

674242 2