

Cutting head, left-hand, System / insert size: DM/16



Order data

Order number	260917 DM/16
GTIN	4251414902756
Item class	29D

Description

Version:

Interchangeable cutting heads for **vibration-damping base bodies**.

Application:

Vibration damping effect up a maximum overhang of **14xD**.

Through-coolant: yes

System: DM

ISO code indexable cutting head: STUCR/L 16

suitable indexable insert: TC.. 16T3..

suitable base body: 264910 – 264922

Minimum pre-drill $\varnothing D_{\min}$: 49 mm

Centre-line offset: 27 mm

Overall length: 32 mm

Technical description

System	DM
Overall length	32 mm
Insert screw	269023 3

suitable indexable insert	TC.. 16T3..
Minimum pre-drill $\varnothing D_{\min}$	49 mm
ISO code indexable cutting head	STUCR/L 16
Insert size	16 mm
suitable base body	264910 – 264922
Centre-line offset	27 mm
Series	Cutting head
Application type	left-hand
Through-coolant	yes
Setting angle κ	93 degrees
Application	Internal longitudinal turning

Accessories

Clamping screw	269433
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cN·m	659906 500
Torx® bit, shank E 6.3 Torx® profile TX15	674248 TX15