

Boring bar base body Steel QC, 5×D, System / shank Ø: QC/32



Order data

Order number	264900 QC/32
GTIN	4251414902350
Item class	29E

Description

Version:

With cooling water connection 1/8-27 NPT.

Note:

$D_{min} = 1/2 \text{ shank } \varnothing + H + \text{cutting head centre-line offset } L_3.$

Through-coolant: yes

System: QC

Overall length L: 268 mm

Centre offset H base body: 6 mm

Assembly bolt: 269025 2

Technical description

Centre offset H base body	6 mm
System	QC
Shank Ø	32 mm
Assembly bolt	269025 2
High-pressure connecting hose	269207
Plug connector for coolant connection	269208
Overall length L	268 mm
suitable indexable insert	264834; 264835
Boring depth up to	5×D
Through-coolant	yes
Type of product	Boring bar shanks

Accessories

PrecisionBit for hex, shank E 6.3 Hexagon 2 mm

674242 2

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659906 500