

Boring bar base body vibration damped, 8×D, System / shank Ø: DM/60



Order data

Order number	264920 DM/60
GTIN	4251414902213
Item class	29E

Description

Version:

With cooling water connection 1/4-18 NPT.

Supplied with:

Reducing adaptor from G1/4 inch to G1/8 inch.

Note:

Do not clamp on the area marked **S**!

$D_{min} = 1/2 \text{ shank } \varnothing + H + \text{cutting head centre-line offset}$

Through-coolant: yes

System: DM

Overall length L_{tot} : 688 mm

Centre offset H base body: 10 mm

non-clamping range S: 254 mm

recommended clamping length: 240 mm

Assembly bolt: 269025 1

Technical description

recommended clamping length	240 mm
non-clamping range S	254 mm
Shank Ø	60 mm
Centre offset H base body	10 mm
System	DM
Overall length L_{tot}	688 mm
Assembly bolt	269025 1
Boring depth up to	8×D

Vibration	damped
Through-coolant	yes

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cN·m	659906 500
Blade for hexagon, shank E 6.3 Hexagon 2 mm	674242 2