

## Cutting head, left-hand, System / insert size: QC/11



### Order data

Order number	260917 QC/11
GTIN	4251414902770
Item class	29D

### Description

#### Version:

Interchangeable cutting heads for **vibration-damping base bodies**.

#### Application:

Vibration damping effect up a maximum overhang of **14xD**.

Through-coolant: yes

System: QC

ISO code indexable cutting head: STUCR/L 11

suitable indexable insert: TC.. 1102..

suitable base body: 264900 – 264908

Minimum pre-drill  $\varnothing D_{\min}$ : 24 mm

Centre-line offset: 13 mm

Overall length: 20 mm

### Technical description

System	QC
ISO code indexable cutting head	STUCR/L 11
Minimum pre-drill $\varnothing D_{\min}$	24 mm

suitable base body	264900 – 264908
Centre-line offset	13 mm
Overall length	20 mm
suitable indexable insert	TC.. 1102..
Insert screw	269022 4
Insert size	11 mm
Series	Cutting head
Application type	left-hand
Through-coolant	yes
Setting angle $\kappa$	93 degrees
Application	Internal longitudinal turning

## Accessories

Clamping screw	269407
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cN·m	659906 500
Torx® bit, shank E 6.3 Torx® profile TX8	674248 TX8