

Cutting head, right-hand, System / insert size: DM/11



Order data

Order number	260408 DM/11
GTIN	4251414902480
Item class	29D

Description

Version:

Interchangeable cutting heads for **vibration-damping base bodies**.

Application:

Vibration damping effect up a maximum overhang of **14xD**.

Through-coolant: yes

System: DM

ISO code indexable cutting head: SDUCR/L 11T3

suitable indexable insert: DC.. 11T3..

suitable base body: 264910 – 264922

Minimum pre-drill $\varnothing D_{\min}$: 49 mm

Centre-line offset: 27 mm

Overall length: 32 mm

Technical description

Insert screw	269023 3
Minimum pre-drill $\varnothing D_{\min}$	49 mm
ISO code indexable cutting head	SDUCR/L 11T3

System	DM
suitable base body	264910 – 264922
Insert size	11 mm
suitable indexable insert	DC.. 11T3..
Overall length	32 mm
Centre-line offset	27 mm
Series	Cutting head
Application type	right-hand
Through-coolant	yes

Accessories

Clamping screw	269433
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cN·m	659906 500
Torx® bit, shank E 6.3 Torx® profile TX15	674248 TX15