

Boring bar base body vibration damped, 10×D, System / shank Ø: DM/40



Order data

Order number	264922 DM/40
GTIN	4251414902121
Item class	29E

Description

Version:

With cooling water connection 1/8-27 NPT.

Supplied with:

Reducing adaptor from G1/4 inch to G1/8 inch.

Note:

Do not clamp on the area marked **S!**

$D_{min} = 1/2 \text{ shank } \varnothing + H + \text{cutting head centre-line offset}$

Through-coolant: yes

System: DM

Overall length L_{tot} : 528 mm

non-clamping range S: 182.9 mm

recommended clamping length: 160 mm

Assembly bolt: 269025 1

Technical description

Overall length L_{tot}	528 mm
recommended clamping length	160 mm
Shank \varnothing	40 mm
non-clamping range S	182.9 mm
System	DM
Assembly bolt	269025 1
Boring depth up to	10×D
Vibration	damped
Through-coolant	yes

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cN·m

659906 500

Blade for hexagon, shank E 6.3 Hexagon 2 mm

674242 2