

Boring bar base body vibration damped, 10×D, System / shank Ø: DM/50



Order data

Order number	264922 DM/50
GTIN	4251414902176
Item class	29E

Description

Version:

With cooling water connection 1/8-27 NPT.

Supplied with:

Reducing adaptor from G1/4 inch to G1/8 inch.

Note:

Do not clamp on the area marked **S!**

$D_{min} = 1/2 \text{ shank } \varnothing + H + \text{cutting head centre-line offset}$

Through-coolant: yes

System: DM

Overall length L_{tot} : 668 mm

Centre offset H base body: 5 mm

non-clamping range S: 215.9 mm

recommended clamping length: 200 mm

Assembly bolt: 269025 1

Technical description

recommended clamping length	200 mm
Overall length L_{tot}	668 mm
Centre offset H base body	5 mm
System	DM
Shank \varnothing	50 mm
non-clamping range S	215.9 mm
Assembly bolt	269025 1
Boring depth up to	10×D

Vibration	damped
Through-coolant	yes

Accessories

Blade for hexagon, shank E 6.3 Hexagon 2 mm	674242 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cN·m	659906 500