

## Cutting head, left-hand, System / insert size: DM/11



### Order data

Order number	260409 DM/11
GTIN	4251414902572
Item class	29D

### Description

#### Version:

Interchangeable cutting heads for **vibration-damping base bodies**.

#### Application:

Vibration damping effect up a maximum overhang of **14xD**.

Through-coolant: yes

System: DM

ISO code indexable cutting head: SDUCR/L 11T3

suitable indexable insert: DC.. 11T3..

suitable base body: 264910 – 264922

Minimum pre-drill  $\varnothing D_{\min}$ : 49 mm

Centre-line offset: 27 mm

Overall length: 32 mm

### Technical description

suitable base body	264910 – 264922
Minimum pre-drill $\varnothing D_{\min}$	49 mm
suitable indexable insert	DC.. 11T3..

Centre-line offset	27 mm
Insert size	11 mm
System	DM
Insert screw	269023 3
Overall length	32 mm
ISO code indexable cutting head	SDUCR/L 11T3
Series	Cutting head
Application type	left-hand
Through-coolant	yes

---

## Accessories

Clamping screw	269433
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cN·m	659906 500
Torx® bit, shank E 6.3 Torx® profile TX15	674248 TX15