

## Boring bar base body vibration damped, 10×D, System / shank Ø: DM/60



### Order data

Order number	264922 DM/60
GTIN	4251414902220
Item class	29E

### Description

#### Version:

With cooling water connection 1/4-18 NPT.

#### Supplied with:

Reducing adaptor from G1/4 inch to G1/8 inch.

#### Note:

Do not clamp on the area marked **S!**

$D_{min} = 1/2 \text{ shank } \varnothing + H + \text{cutting head centre-line offset}$

Through-coolant: yes

System: DM

Overall length  $L_{tot}$ : 808 mm

Centre offset H base body: 10 mm

non-clamping range S: 254 mm

recommended clamping length: 240 mm

Assembly bolt: 269025 1

### Technical description

non-clamping range S	254 mm
Overall length $L_{tot}$	808 mm
Shank Ø	60 mm
Centre offset H base body	10 mm
System	DM
recommended clamping length	240 mm
Assembly bolt	269025 1
Boring depth up to	10×D

Vibration	damped
Through-coolant	yes

---

## Accessories

Blade for hexagon, shank E 6.3 Hexagon 2 mm	674242 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cN·m	659906 500