

Cutting head, right-hand, System / insert size: DM/12



Order data

Order number	260008 DM/12
GTIN	4251414902404
Item class	29D

Description

Version:

Interchangeable cutting heads for **vibration-damping base bodies**.

Application:

Vibration damping effect up a maximum overhang of **14xD**.

Through-coolant: yes

System: DM

ISO code indexable cutting head: SCLCR/L 12

suitable indexable insert: CC.. 1204..

suitable base body: 264910 – 264922

Minimum pre-drill $\varnothing D_{\min}$: 49 mm

Centre-line offset: 27 mm

Overall length: 32 mm

Technical description

ISO code indexable cutting head	SCLCR/L 12
Insert size	12 mm
Insert screw	269022 3

suitable indexable insert	CC.. 1204..
System	DM
suitable base body	264910 – 264922
Overall length	32 mm
Centre-line offset	27 mm
Minimum pre-drill $\varnothing D_{\min}$	49 mm
Series	Cutting head
Application type	right-hand
Through-coolant	yes

Accessories

Clamping screw	269406
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cN·m	659906 500
Torx® bit, shank E 6.3 Torx® profile TX15	674248 TX15